



ADJUST R2 using 100khz sq wave 1V input

ADJUST bias trim for sym PP aprox 40v or harmonic content using FFT

Note: Pre-amp values shown

For Power amp use 1000uF output cap and 0 ohm for R8

and change R5 - R10 to 8-10 ohm each

Adjust for desired power level

Hybrid pre-amp/power-amp AS-BUILT point 2 point

TITLE: Hybrid-SZpre-V0.61

Document Number:

REV:

Date: 6/16/16 11:16 PM

Sheet: 1/1