

Input PCB for Purifi 1ET400A

Settings

For SMPS1200 control AMP/ON on

Set J3.2 ON, set OFF to use Extern AMP/ON

For DC/Fatal protection to powerdown the SMPS1200

Set J3.1 ON, otherwise OFF

Connections

H1 to Purifi 1ET400A

H2 to J1 Hypex SMPS1200A400

H3 to J4 Hypex SMPS1200A400

Parts

R1,R2 = 1k

C1,C2 = 100uF/100V

C1,C2,C3,C4 = 10uF/16V

D1,D2 = 3mm Led

J1 = 2 pol Dipswitch

XLR 1,XLR 2 = Neutrik NCJ 6 FAH

H1,H4 = Header 36 pol type SSW-118-02-T-D-RA

H2 = Header 6 pol type JST-B06P-VL

H3 = Header 10 pol type T821110A1S100CEU

H6 t/m H9 = 6.3mm faston

H5 = 2 pins header

